




















SINCE 1954

The citrus juicer #71C is easy to use and very silent.

To use everywhere you need a fresh squeezed citrus juice: health food stores, hotels, bars, restaurants, cafeterias, ice cream shops, institutions, hospitals and even at home.



THE PROFESSIONAL ART OF JUICING SINCE 1954

You will find the citrus juicer of your need to make citrus juices either in a glass or in a jug.

Equipped with powerful asynchronous motors, these appliances allow you to squeeze all types of citrus: lime, lemon, orange or grapefruit.

All of these juicers are easy to use and clean: all the parts which are in contact with the fruits are removable.





























EASY TO USE - EASY TO CLEAN - COMPLETELY SAFE

www.santos.fr

A juicer that you can clean quickly and easily.

Just wash the main different parts of the top that you can remove from the base in a simple movement: bowl, grid, ring and squeezer.







60 years of wordlwide experience on the juice market: all Santos juicers keep flavour and all vitamins from fruits.

TECHNICAL SPECIFICATIONS



Motor


Single phase: 110-120 V - 50/60 Hz - 40 W - CE220-240 V - 50/60 Hz - 40 W - CE

Speed: 80 rpm (50 Hz)



Weight

Net: 3.5 Kg (7.7 lbs) Packed: 3.9 Kg (8.6 lbs)



APPLIANCE D: 236 mm (9") W: 170 mm (7") H: 310 mm (12")



SHIPPING BOX D: 260 mm (10") W: 190 mm (7.5") H: 330 mm (13")

SAFETY, STANDARDS, HYGIENE

In accordance with the following regulations:

Machinery directive 2006/42/EC Electromagnetic compatibility 2004/108/EC "Low voltage" directive 2006/95/EC Regulation 1935/2004/EC (contact with food) RoHs directive 2002/95/EC

Harmonized European standards:

EN ISO 12100 - I AND 2:2004

EN 60204-1 : 2006

CE (European standards)

Thermal safety

Motor protected by internal thermal detector

Electrical safety

- On/Off interlock switch is waterproof
- All mechanical parts are ground (earth) connected
- All equipment is 100% tested at the end of assembly (special electrical testing bay)

Acoustic safety


Silent moto réductor asynchronous motor

Hygiene

All removable parts can be put in a dishwasher or easily cleaned with hot soapy water.



www.santos.fr



SANTOS

140-150 Avenue Roger Salengro – 69120 VAULX-EN-VELIN (Lyon) – FRANCE – TEL. +33 472 37 35 29 – FAX. +33 478 26 58 21 **Website:** www.santos.fr – **Email:** santos@santos.fr